



USB Type B 2.0, Male Connector Modular


Item No. 2001C202



mm±0.2



| PIN NUMBER | SIGNAL NAME |
|------------|-------------|
| 1 | VBUS |
| 2 | D- |
| 3 | D+ |
| 4 | GND |



Material:
Housing: PP
Insulator: PBT+25%GF
Connector shell: SPCC with plated Ni 40µ min.
Contact: Brass with plated Au1µ
Technical:
Voltage rating: 5V max.
Current rating: 2A max.
Contact resistance: 20mΩ max.
Insulation resistance: 1000MΩ min.
Dielectric withstanding voltage: 500V/AC(R.M.S)
Operation temperature: -20 ~85°C