

# PRODUCT SPECIFICATION

**Carl  
Kammerling**  
International

<b>Brand</b>	KASP
<b>Product Range</b>	Heavy Duty Combination Padlock
<b>Catalogue number</b>	117
<b>Date</b>	19/03/2009

## Range Description

Resettable combination padlocks

## Features

- Hardened Steel Shackle - Extra protection against hacksaw & cropping attacks
- Double Bolted Locking Mechanism - Extra strength to resist torsion & pull attacks
- Anti Manipulation Locking System - Protects against manipulation attack
- 4 Dial Resettable Combination - Resettable combination for added convenience & security
- Rust Free Internal Components - Extra resistance against corrosion

The padlock is supplied display packed, in sealed blister packs.



Technical product information

**Body** – Die Cast, Chrome plated

**Shackle** - Hardened steel, Chrome plated

**Locking mechanism** - Double bolted, 4 dial combination locking mechanism featuring an anti-manipulation locking system to prevent intelligent manipulation attack.

**To open the padlock:**

1) Using the correct combination code, open the padlock by aligning the dial wheels with the indicators on the lock body (pre-set factory combination code 0-0-0-0) and depress the shackle

**To lock the padlock:**

1) Whilst in the open position, scramble the dial wheels and depress the shackle into the body of the padlock until it locks

**To reset the lock to a combination of your choice:**

1) Open the padlock using the preset combination code

2) Insert the change key into the keyhole on the side of the padlock

3) Firmly press the key into the keyhole and turn 90 degrees clockwise or anti-clockwise. *[IMPORTANT: Ensure the change key is fully depressed to avoid losing the combination]*

4) With the change key held at 90 degrees, reset the dials wheels to a combination of your choice (we recommend that you record your new combination code and store it in a safe place)

5) With your new combination code set, turn the change key through 90 degrees back to its original position and withdraw it from the key hole

6) Lock the padlock by scrambling the dial wheels and depressing the shackle into the body of the padlock until it locks

**Security rating:**

Type	Security rating
K11750D	6

**Shackle Dimensions:**

Dimensions mm	Shackle			Body
	Dia	Internal width	Internal height	Width
K11750D	8	25	25	50

**Use environment** - Normal outdoor use √√

**Recommended applications**- Lockers, sheds, gates, garages

Standards compliance

None applicable

User health and safety information

None applicable

RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	KASP padlocks are guaranteed against defects in manufacture and/or materials for 10 years Damage caused through inappropriate use or attempted break in is not covered
Country of origin	Taiwan

## Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
K11750D	50	25	75	246	118	27	186	290