


PVC-Klebefittings

T-Stücke, reduziert mit Klebemuffen, PVC-U

PN 16




Achtung: Nicht für Druckluft oder andere Gase unter Druck geeignet!



Typ	Innen Ø d	Innen Ø d1	Außen Ø D	Baulänge L	Baulänge L1	Z
PVCT 201620	20	16	28	27	25	11
PVCT 251625	25	16	33	33	30	14
PVCT 252025	25	20	34	33	30	14
PVCT 322032	32	20	42	41	34	18
PVCT 322532	32	25	42	41	37	18
PVCT 402040	40	20	50	48	37	21
PVCT 402540	40	25	51	47	40	21
PVCT 403240	40	32	50	48	43	21
PVCT 502550	50	25	61	57	45	26
PVCT 503250	50	32	61	57	48	26
PVCT 504050	50	40	61	57	52	26
PVCT 633263	63	32	74	71	55	33
PVCT 634063	63	40	74	71	59	33
PVCT 635063	63	50	74	71	64	33
PVCT 754075	75	40	90	84	65	39
PVCT 755075	75	50	90	84	70	39
PVCT 756375	75	63	90	84	77	39
PVCT 905090	90	50	106	98	78	47
PVCT 906390	90	63	106	98	86	47
PVCT 907590	90	75	106	98	90	47
PVCT 11050110	110	50	129	118	88	57
PVCT 11063110	110	63	130	117	90	56
PVCT 11075110	110	75	130	117	100	56
PVCT 11090110	110	90	130	117	107	56

4



Verbinder mit Klebemuffen, PVC-U

PN 16



Achtung: Nicht für Druckluft oder andere Gase unter Druck geeignet!

Typ	Innen Ø d	Außen Ø D	Baulänge L
PVCMU 16	16	23	31
PVCMU 20	20	26	36
PVCMU 25	25	33	42
PVCMU 32	32	41	48
PVCMU 40	40	51	57
PVCMU 50	50	60	66
PVCMU 63	63	74	80
PVCMU 75	75	88	92
PVCMU 90	90	105	107
PVCMU 110	110	128	127