

LUGS 16 FOR SIGNAL TRANSFER 250V/8 A


Mounting rail/pluggable spring clamps


16-pole

Push-In spring clamp terminals

[Link to Product](#)

Illustration





Product may differ from Image

Technical Data

Operating voltage	max. 250 V AC
Operating current per bit	max. 8 A
Material group	(EN 50178) over voltage, category I

General data

Connection	Spring clamp plug-in terminals: max. 2.5 mm ² (AWG 14)
Mounting method	DIN-rail mountable (EN 60715)
Dimensions H × W × D	75×45×75 mm
Temperature range	-20...+60 °C

Commercial data

country of origin	CZ
customs tariff number	85369010
minimum order quantity	1