

THB.392.A4A

Micro series power distributor, 1 input 3 output, sealed interconnections, IP68



SPECIFICATION

Cable Entries	4
Number of Poles	4
Terminal Type	Screw
Body Material	PA66 GF UL94V0 / UL94 V2, Caps / TPE Seals
Colour	Black and green
IP Rating	68
Max Conductor Size (Sq mm)	4
Max Current (A)	17.5
Max Voltage (V)	450
Minimum Temp Rating °C	-40
Max Temp Rating °C	125
Minimum Cable Diameter (mm)	8
Maximum Cable Diameter (mm)	12
Depth (mm)	28
Fixing System	Screw
Length (mm)	80
Temperature "T" Rating	T85
Width (mm)	54