

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191600012](#)
Status: **Active**
Overview: [Splices](#)
Description: Closed-End Insulated Splice for 14-22 AWG Wire, Clear

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-19408-109-001 \(PDF\)](#)
[Product Specification 194130096-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-013-001 \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Splices
 Series [19160](#)
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview [Splices](#)
 Product Name Closed-End Insulated
 UPC 800753110229

Physical

Barrel Type Closed
 Color - Resin Natural
 Flammability 94V-2
 Insulation Nylon (PA)
 Material - Metal Copper
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 0.454/g
 Packaging Type Carton
 Temperature Range - Operating 105°C
 Wire Insulation Diameter 6.10mm max.
 Wire Size AWG 14, 16, 18, 20, 22

Electrical

Voltage - Maximum 300V

Material Info

Engineering Number NC-2214

Reference - Drawing Numbers

Packaging Specification PK-19408-109-001
 Product Specification 194130096-000, PS-19902-013-001
 Sales Drawing SD-19160-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/01/2018 (15
 January 2018)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
Prop65	Missing Compliance Data
RoHS Phthalates	Not Contained

Search Parts in this Series

[19160 Series](#)