

TACT AND KEY SWITCHES

PRODUCT NUMBER 3006.2106



TECHNICAL DATA

Product number	3006.2106
Business unit	Automotive switches
Product Manager	-
Product family	Tact and key switches
Actuation type	direct
Packing unit	1 800
Miscellaneous	LED white
Weight	.360 g
ROHS conform	yes
Output	catalog before 2009 / catalog
Switching function	Normally open contact (SPNO)
Material fixed contact	gold-plated
Number of poles	1 - pole
connections	SMT
Mechanical life endurance	50E4
Rating IEC	50 mA 28 V
Contact resistance (new condition)	< 100 mOhm
Protection type	→ Connection IP 40 → Actuator IP 40
Ambient temperature	→ connection side -40 °C ... +95 °C
Storage temperature	-40 °C ... +95 °C
Actuators and additional actuators	standard actuator
Connection surface	→ bearing connection gold plated → external connection gold plated
Contact material	gold plated
Contact distance	< 3 mm
Lighting	function illumination: LED (Vishay), T 1, white

Contact type	jump contact
Operating force	4 +1 -0.5 N
Bounce time	< 5 ms
Free position (FP) max.	4.15 mm
Operating position (OP)	3.2 ±0.2 mm
Permissible total travel position	2.9 mm
Total travel / stroke	1.0 mm
Release force	≥ 1.0 N
Miscellaneous	with pressure point
Additional labeling packing	4 N, weiße LED, T1 4 N, white LED, T1

Technical changes reserved. Dimensions are not binding.
Detailed specifications available on request.

Marquardt GmbH · Schloss-Straße 16 · 78604 Rietheim-Weilheim · Germany
Phone: +49 (0) 7424 / 99-0 · Fax: +49 (0) 7424 / 99-2399 · www.marquardt.com · marquardt@marquardt.de