

J.21 | J - 3/8" metric 12-point sockets



Standards:

NF ISO 2725-1, NF ISO 1711-1,
ISO 2725-1, ISO 1711-1, DIN
3124, ASME B107.5

Description:

- OGV® profile: more powerful tightening, preserves fasteners.
- Finish: bright chrome.

	J.21
A [mm]	21.0
Diameter [mm]	23.5
Diameter D1 [mm]	28.5
Length L [mm]	33.0
Length L1 [mm]	16.0
12-Point [mm]	12.0
Weight [g]	75.0