


Within Series Adaptor 34_SK-50-0-51/199_N

Description

Bulkhead adaptor jack/jack
SK jack (female) / SK jack (female)

For Test & Measurement applications
Precision adaptor

Interface standard
Series SK - MIL-STD-348A/323



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	40 GHz
VSWR	DC - 40 GHz ≤ 1.02 + 0.01 f (GHz)

Mechanical Data

Number of matings	500
Weight	0.0042 kg

Environmental Data

Operating temperature	-40 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - SK jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PPE (Polyphenylene ether, PPO)	

Interface - SK jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PPE (Polyphenylene ether, PPO)	

Related Documents

Outline drawing	DOU-00013638
Mounting hole	DOU-00008731

Ordering Information

Single package	34_SK-50-0-51/199_NE
----------------	----------------------