

HUBER+SUHNER® DATA SHEET

Coaxial PCB Connector: 81_MMCX-50-0-1/111_O

Rev.: A 

Description

Straight PCB plug

Interface standards
SUHNER-MMCX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Board mounting type through holes
Weight 0.0008 kg

Environmental Data

Operating Temperature -55 °C to 155 °C

Material Data

Piece Parts

Centre contact
Outer contact
Body
Insulator

Material

Copper Beryllium Alloy
Brass
Brass

Surface Plating

Gold Plating (Nickel underplated)
Gold Plating
Gold Plating

Related Documents

Outline drawing DOU-00013167
Catalogue drawing DCA-00013169
Mounting hole DOU-00012639

Ordering Information

Single package 81_MMCX-50-0-1/111_OE

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.

HUBER+SUHNER – Excellence in Connectivity Solutions



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com