


Inset Kit LED IP23

INSET TREND KIT SW REFLED ES50 36° BN WW DIM
3001762



Product features

- GU10 Housing with REFLED ES50 36° lamp included, Ideal for indoor application, Loop in - loop out box included



PRODUCT OVERVIEW

Product name	INSET TREND KIT SW REFLED ES50 36° BN WW DIM
Technology	LED
Cap/Base	GU10
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Residential & Consumer
ETIM Class	EC001744
E-number FI	4271313
E-number SE	7467393
Warranty	3 years
Fixture luminous flux (lm)	345
Luminaire efficacy (lm/W)	76
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Beam Angle (°)	36
Photobiological Risk Group	RG1
Light source included	0029126
Total power consumption (W)	4.5
Electrical protection	Class II
Control gear type	LED driver constant current
Dimmable	No
Dimming method	Mains: leading / trailing edge
Housing colour	White
IP rating	IP23/20
IK rating	IK02
Product EAN number	8711971017622

Inset Kit LED IP23

INSET TREND KIT SW REFLED ES50 36° BN WW DIM
3001762

DATA TABLE

General data

Product name	INSET TREND KIT SW REFLED ES50 36° BN WW DIM
Technology	LED
Cap/Base	GU10
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Residential & Consumer
ETIM Class	EC001744
E-number FI	4271313
E-number SE	7467393
Warranty	3 years

Optical data

Fixture luminous flux (lm)	345
Luminaire efficacy (lm/W)	76
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Adjustable chromaticity	N
Beam Angle (°)	36
Distribution type	Symmetric
Photobiological Risk Group	RG1

Electrical data

Light source included	0029126
Total power consumption (W)	4.5
Mains voltage (V)	220-240V
Electrical protection	Class II
Control gear type	LED driver constant current
Transformer required	Yes
Dimmable	No
Dimming method	Mains: leading / trailing edge
Glow Wire Test (°C)	650
Energy Efficiency Class (A->G) of contained light source	F

Physical data

Housing colour	White
IP rating	IP23/20
IK rating	IK02
Diffuser finish	Other
Diffuser material	None
Reflector finish	None
Nominal Product Height (mm)	85

Inset Kit LED IP23

INSET TREND KIT SW REFLED ES50 36° BN WW DIM
3001762

Nominal Product Diameter (mm)	83
Cutout Dimensions (W x L in mm or Diameter in mm)	75
Weight (kg)	0.179
Recessed Depth (mm)	100

Packaging

Single packaging type	Carton
Product EAN number	8711971017622
Packaging single length / height (cm)	13.13
Packaging single width (cm)	9.9
Packaging single depth (cm)	8.4
DUN14 (outer)	18711971017629
Units per outer package	30
Packaging outer length / height (cm)	28.5
Packaging outer width (cm)	28.7
Packaging outer depth (cm)	53.0

PHOTOMETRY

TECHNICAL DRAWINGS

