

Clamping tool assortment in box



Application:

This assortment contains all of the requisite elements for quick clamping of workpieces or equipment on T-groove tables.

Execution:

- All parts made of heat-treated steel

Delivery:

Assortment in wooden case



Art. no.	26153 018
Brand	AMF
Manufacturer Part Number	83626
Suitable for groove width	18
Min. clamping height with 2 clamping points	2 mm
Thread dimension	M16
Max. clamping height with 2 clamping points	270 mm
Min. clamping height with 4 clamping points	2 mm
Max. clamping height with 4 clamping points	160 mm
Wooden box length	510 mm
Wooden box width	415 mm
Wooden box height	50 mm
Number of DIN 787 T-slot screws	2 x 63 mm, 4 x 100 mm, 4 x 160 mm
Weight	21.5 kg
Number of DIN 6379 stud bolts (extension pin)	4 x 125 mm
Number of DIN 6330 B high nuts	6 PCS
Number of rounded washers and ball sockets DIN 6319 G	6 PCS
Number of extension nuts	4 PCS
Gross Weight	21.800 kg
Product Group	260

EAN

4020772083625