

Micrometer

Adjustable anvil

Mitutoyo

Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces
- Spindle travel 50 mm

Advantage:

- Sturdy, robust and lightweight construction for large measurement ranges

Delivery:

Includes box, two setting standards



Art. no.	32016 123
Brand	MITUTOYO
Manufacturer Part Number	105-413
Min./max. length measuring range	1500-1600 mm
Vernier scale	0.01 mm
Measuring surface diameter	8 mm
Measuring spindle increments	0.5 mm
Spindle clamping	Yes
Error limit	27 µm
Display	Nonius
Min./max. measurement force	5-10 N
Calibration Group	D
Gross Weight	63.000 kg
Product Group	3MA

EAN

4946368007618