

Ultrasonic wall thickness gauge MTG 4

For separate measuring heads

elcometer®

Application:

For non-destructive recording of the material thickness of a wide range of acoustically conductive materials such as metals, NF metals, ceramic, plastics, glass, etc. Ideal for monitoring corrosion and erosion on closed components and structures or those accessible only from one side, e.g. pipes, tanks, large metal sheets etc.

Execution:

- Robust ABS plastic housing
- Large, easy-to-read 2.4" colour display
- IP 54 degree of protection, splash-proof
- Integral zero disc
- Red/green LEDs on the housing, for displaying the upper and lower limit value

Advantage:

- Easy to use
- High measuring accuracy
- Efficient measurement



Art. no.	46100 110
Brand	ELCOMETER
Manufacturer Part Number	MTG4
Min./max. Pulsed-Echo (P-E) measuring range	0.63-500 mm
Min./max. Echo-Echo ThruPaint (E-E) measuring range	2.54-25.4 mm
Resolution of wall thickness	0.1 mm
Gross Weight	0.754 kg
Product Group	451