

Permanent NEO lifting magnet

3-fold safety

Application:

For the secure lifting of sheet metals, profiles, panels, round- and bar-shaped parts or for loading and unloading machines.

Advantage:

- Large lifting capacity with low tare weight and small dimensions
- Robust, low-maintenance, user-friendly
- Easy to switch on and off using the hand lever, with safety lock

Delivery:

With test certificate

Art. no.	77301 013
Load-carrying capacity	300 kg
Load-carrying capacity for round materials	150 kg
Tear-off weight certified	1000 kg
For min./max. round material diameter	60-200 mm
Suitable for min. sheet metal thickness	4 mm
Surface area length	152 mm
Surface area width	100 mm
Height up to load hook	164 mm
Colour	Orange

EAN-Code

0705632164426

