



Audible & Visual Alarms

Technische Daten / technical data:	B/SE128	B/SE128AC
Spannungsbereich / <i>operating voltage</i> (DC) (V)	10...30 VDC	98...260 VAC
Stromaufnahme / <i>current consumption</i> (mA)	< 32	< 50
Tonanzahl / <i>signalling Tones</i> (2 Ton ansteuerbar / <i>2 tone selectable</i>)	28	28
Lautstärke / <i>sound pressure level (SPL)</i> (dB / 1m)	101	101
Schutzklasse / <i>ingress protection</i>	IP 65	IP 65
Abmessungen / <i>dimensions</i> (mm)	Ø 101 x 100	Ø 101 x 100
Zertifizierungen / <i>approvals</i>	VdS Nr. G200117 / CE VdS No. G200117 / CE	- -
Gehäusefarbe(n) / <i>housing colour(s)</i> (RAL 3001) (RAL 9010)	Rot / <i>red</i> Weiß / <i>white</i>	Rot / <i>red</i> Weiß / <i>white</i>

