


# Power Strip

6xT13, 3 m, Type 12/Protective contact



With 10 A protector (thermo fuse)  
Reconnectable with internal supply terminals  
Impact resistant and halogen-free case  
Flexible positioning in racks, rear walls and housing frame  
Fastening clips included  
In accordance with the Swiss Ordinance on Low-Voltage Electrical Equipment (CVEO), approved by the Swiss Federal Inspectorate for Heavy Current Installations



## SPECIFICATION:

No. of sockets	6
Socket type	T13
Colour	black
Cable length	3 m
Plug type	Type 12/Protective contact
Rated output	2.5 kW
Load capacity	10 A/230 VAC
Dimensions L x W x H	434 x 44.4 x 44.45 mm
Socket arrangement	Lengthwise
Connecting cable	H05VV-F. 3G 1 mm <sup>2</sup>
Material	Aluminium/Polypropylene
Assembly type	19" System
Mounting	Horizontal/Vertical
Approvals	S+ ESTI 17.0241

**Art. Nr.**

**RND 465-00213**

