

Accessories

i-Con Soldering Irons

ERSA®

ERSA®



0100CDJ

- ERSA i-Tool soldering iron**
- 150 W Micro Heating Element
 - Ultra fastest heat up and recovery
 - "One Touch" Easy to Use operation
 - Automatic Standby Motion Sensor
 - 24V, weight 30g



0450MDJ

- ERSA Chip-Tool SMT desoldering pincette for low-temperature, safe SMD soldering**
- ergonomic and precision repair
 - weight 70g



0720ENJ

- ERSA X-Tool desoldering iron**
- High-power, low-temperature, safe through-hole desoldering
- 120 W
 - Vacuum 800mBar
 - max. temperature 350°C
 - 24V, weight 240g

Part No.	Ord.No.
0 0100CDJ	64112
0 0450MDJ	64124
0 0720ENJ	64121

ERSA Miscellaneous Soldering Irons.



270 BDJ

- 20W ERSA Micro Tool Soldering Iron**
- for DIG20A, SMT60A, TW80A with 212BD Tip (0,4mm Conical)
- Supply 24V



21100J

- Spare Heating Element for ERSA Micro tool 270BDJ**
- 24 V, 20 W



670 CDJ

- 60W ERSA Basic Tool Soldering Iron with 832CD Tip (2,2mm Chisel)**
- Suitable for ANA 60
- Power Supply: 24V
- Heating time 60s
- Max. Temperature 350°C
- Suitable Tips: 832, 842 series



890CDJ

- 80W Soldering iron RT 80 with soldering tip 842 CD (2,2mm Chisel)**
- Suitable for RDS-80.
- Power Supply: 24V
- Heating time: 40s
- Max. Temperature: 450°C
- Suitable Tips: 832, 842 series

Part No.	Ord.No.
0 270 BDJ	40189
0 21100J	7113
0 670 CDJ	40164
0 890 CDJ	64125

ERSA Holders



A39

- RH-80 Iron Holder for RT-80 irons**



A48

- Iron Holder for i-Tool irons**


Part No.	Ord.No.
0 A 39	64127
0 A 48	64128

Soldering Tips

ERSADUR Soldering Tips Serie 212

Pb free


Suitable for: ANALOG 20A, SMT 60A/AS, DIG20A, REWORK 80 and Micro Tool soldering iron



Chisel



Conical




MicroWell

MICROWELL - Specially designed SMD Soldering Tip. It is possible to solder one side, sometimes even whole component, without interruption. You don't have to pre-tin the pads or have to take soldering paste, because the solder will be delivered from the solder deposit on the tip.


Part No.	Ord.No.	Description
S 212 BD LF	39013	0,4mm Conical
S 212 CD LF	39014	1,0mm Chisel
S 212 ED LF	39015	1,8mm Chisel
S 212 MS LF	4347	2,3mm Micro Well

ERSADUR Desoldering Tips Serie 422


Suitable for ERSA i-CON, SMT 60 A / AS, DIG 20 A... for desoldering tweezers 40. Price is for one pair.



elliptical-shaped




conical



chisel

17,5 x 17,5



angular

Part No.	Ord.No.	Description	for desoldering
0 422 MD	39029	2mm, elliptical	MELF, MiniMELF
0 422 SD	46934	0,2mm, conical	MICROMELF
0 422 ED	39017	6mm, chisel	SOIC 8
0 422 FD 2	39021	15mm, chisel	SOIC 24
0 422 FD 3	39018	7,5mm, chisel	SOIC 12/SOT23
0 422 FD 4	39020	12,5mm, chisel	SOIC 20
0 422 FD 5	39022	17,5mm, chisel	SOIC 28
0 422 FD 6	39023	20mm, chisel	SOIC 32
0 422 FD 7	3280	25mm, chisel	25mm long comp
0 422 FD 8	42912	27,5mm, chisel	27,5mm long comp
0 422 QD 1	39025	12,5mm, 90° angle	PLCC 28
0 422 QD 2	39028	25mm, 90° angle	PLCC 68
0 422 QD 3	39026	17,5mm, 90° angle	PLCC 44
0 422 QD 4	39027	20mm, 90° angle	PLCC 52
0 422 QD 5	39024	10mm, 90° angle	PLCC 20
0 422 QD 6	40868	15mm, 90° angle	QFP, TQFP
0 422 QD 7	40869	30mm, 90° angle	PLCC 84
0 422 RD 1	40870	22,5x16,5mm	QFP100
0 422 RD 2	6611	15x12,5mm	PLCC32