

Product Specification



602CHXX

Jumbo Specification

Champagne UHS

<u>Property</u>	<u>Value</u>			<u>Method</u>
	<u>LL</u>	<u>MP</u>	<u>UL</u>	
Thickness (inches)	1,00	1,08	1,15	Guston Bacon
Weight (oz/yd ²)	22	26	30	Scale
Color (Standard)*	Champagne			Visual
Fiber Type	25 % Polyester PET Recycl. - 75 % virgin Polyester			
Resin System	Cross-link water base			
Abrasive	N/A			
Tensile (lb/2 in)	> 45			
Jumbo Length	70			yds.

* Color: (1) Standards established with lightest shade, target & darkest shade
(2) Standards to be updated every six (6) months if necessary

Finished Good Specification

Champagne UHS

<u>Property</u>	<u>Value</u>			<u>Method</u>
	<u>LL</u>	<u>MP</u>	<u>UL</u>	
Thickness (inches)	1,00	1,08	1,15	Guston Bacon
Weight (oz/yd ²)	22	26	30	Scale
Color (Standard)*	Champagne			Visual
Outside Dimension	-0,125	0	0,125	Inches
Inside dimension	3,2	3,25	3,3	Inches
Cure test	5% Pinesol Solution			Boil
Bleed Tolerance	None			
Temperature	212 deg F (+)			
Test Time	5 Minutes			
Test Pad	3"			

- * Color: (1) Standards established with lightest shade, target & darkest shade
- (2) Standards to be updated every six (6) months if necessary

