


## POTENTIAL TERMINAL BLOCK BLUE YELLOW

Potential terminal block  
blue/yellow

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Approvals



#### Technical Data

Operating voltage	max. 30 V AC/DC
Total current	max. 10 A

#### General data

Protection	IP20
Dimensions H × W × D	70×56×32.5 mm
Connection	Spring clamp terminals: 0.08...2.5 mm <sup>2</sup> (AWG 28...12)

Temperature range 0...+55 °C (storage temperature -40...+85 °C)

**Commercial data**

country of origin	DE
customs tariff number	85369010
minimum order quantity	1