

PLUG-IN RELAY, 2 CO CONTACTS, 115V AC, 16A,  
WIDTH 15.5MM, PT RANGE



Figure similar

### General technical data:

Supply voltage frequency for auxiliary and control current circuit Rated value		
• minimum	Hz	50
• maximum	Hz	60
<b>Type of voltage</b>		AC
<b>Control supply voltage</b>		
• with AC		
— at 50 Hz Rated value		
— minimum	V	115
— maximum	V	115
— at 60 Hz Rated value		
— minimum	V	115
— maximum	V	115
Number of NC contacts for auxiliary contacts		0
Number of NO contacts for auxiliary contacts		0
Number of CO contacts for auxiliary contacts		2
Operating current of the auxiliary contacts		
• at AC-15		
— at 230 V	A	2.5
<b>Design of the switching function positively driven</b>		No
<b>Switching behavior</b>		monostable

### Mechanical data:

<b>Type of electrical connection</b>		screw-type terminals
<b>Design of the relay operating mechanism</b>		poled

Product component Plug-in socket		No
Width	mm	12.7
Height	mm	12.7
Depth	mm	19.5

#### Certificates/ approvals:

General Product Approval	other
--------------------------	-------



[Declaration of Conformity](#)

#### Further information

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

##### Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

##### Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=LZX:RT424615>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/LZX:RT424615>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=LZX:RT424615&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=LZX:RT424615&lang=en)

last modified:

15.01.2015