

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300580025](#)  
**Status:** **Active**  
**Description:** Ultra-Lock (M12) D-Coded to RJ-45 Adapter, Straight to Straight, 4 PoleFemale to RJ45 Male, 1.0m (3.28') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E200650

**General**

Product Family Industrial Receptacles  
 Series [130058](#)  
 IP Rating IP67  
 Product Name RJ45, Ultra-Lock (M12)  
 Type Adapter  
 UPC 78678802441

**Physical**

Coupling Type Push to Lock  
 Gender Female-Male  
 Keyway D-coded  
 Length 1.0m  
 Material - Component Nylon  
 Mounting Thread Size N/A  
 Net Weight 150.000/g  
 Orientation Straight  
 Panel Mount N/A  
 Poles 4  
 Temperature Range - Operating N/A  
 Wire Size AWG N/A  
 Wire/Cable Type N/A

**Electrical**


Current - Maximum per Contact N/A  
 Voltage - Maximum N/A

**Material Info**

Engineering Number ERWPAB3002M010

**Reference - Drawing Numbers**

Sales Drawing SD-130054-002



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

50 Image

Not Relevant

Not Contained

**Search Parts in this Series**

[130058](#) Series