

Product information

30 16 160


- Heavy duty and wear resisting
- Different jaw styles
- Long, trapezoidal jaws
- Chrome vanadium electric steel, forged, oil-hardened

Long Nose Pliers

DIN ISO 5745 IEC 60900 DIN EN 60900



General	
Article No.	30 16 160
EAN	4003773001904
Pliers	chrome-plated
Head	chrome-plated
Handles	insulated with multi-component grips, VDE-tested
Weight	150 g
Dimensions	160 x 57 x 18 mm
Standard	DIN ISO 5745 DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Jaw thickness (joint) (T1)	9.5 mm
Tips width (W4)	3.0 mm
Tips thickness (T2)	5.0 mm
Jaw length (L3)	46.5 mm
Head width (W3)	16.5 mm



technical change and errors excepted