

Profile Deep Wide Surface 30

Profile Deep Wide Surface 30 CDE-9/T 3m anodised
0022608



Product features

- A deep wide 3000mm length anodised aluminium lighting profile that can be combined with multiple click diffusers (flat opal - 0022624, round frosted - 0022625, square opal - 0022633) with a maximum LED strip width of 20mm. Can be mounted with 'Profile HO surface 16 raw alu.' or dedicated plates. Additional accessories like end caps, profile holders or mounting brackets need to be ordered separately.



PRODUCT OVERVIEW

Product name	Profile Deep Wide Surface 30 CDE-9/T 3m anodised
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
Warranty	3 years
Housing colour	Silver
Product EAN number	5410288226088

DATA TABLE

General data

Product name	Profile Deep Wide Surface 30 CDE-9/T 3m anodised
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
Warranty	3 years

Physical data

Housing colour	Silver
Nominal Product Length (mm)	3000
Nominal Product Width (mm)	33.4
Nominal Product Height (mm)	29.6
Weight (kg)	0.74

Packaging

Single packaging type	Carton
Product EAN number	5410288226088
Packaging single length / height (cm)	300.0
Packaging single width (cm)	3.0
Packaging single depth (cm)	2.0

Profile Deep Wide Surface 30

Profile Deep Wide Surface 30 CDE-9/T 3m anodised

0022608

DUN14 (outer)	05410288226088
Units per outer package	20
Packaging outer length / height (cm)	305.0
Packaging outer width (cm)	16.0
Packaging outer depth (cm)	16.0

TECHNICAL DRAWINGS

