

Electronic outside micrometer

with disc-shaped measuring faces

Mitutoyo

Application:

For measuring tooth span on cogs, for recesses, groove distances etc.

Execution:

- measuring faces made of hardened steel
- ABS function
- HOLD (measured value storage)
- Origin (measurement presetting)
- IP65
- Digimatic

Advantage:

- Accesses hard-to-reach measuring points

Delivery:

Includes box, adjustment wrench, standard setting (25 mm or more), adjustment wrench, battery



Art. no.	32017 568
Brand	MITUTOYO
Manufacturer Part Number	369-251-30
Display	Digital
Min./max. length measuring range	25-50 mm
Digit increment	0.001 mm
Measuring surface diameter	6.3 mm
Measuring arrangement	Plate
Material of measuring bolt	Steel
IP protection class	IP 40
Data transmission type	DIGIMATIC
Spindle clamping	Yes
Digit height	7.5 mm
Functions	ABS function, Origin (Dimension preset), Hold-function (AE lock), Automatic switch-off
Min./max. measurement force	3-8 N
Error limit	4 µm
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
DIN	863
Bracket depth	47 mm
Measuring spindle increments	0.5 mm
Calibration Group	D
Gross Weight	0.890 kg
Product Group	3MA

EAN

4946368689623