

## Precision scales EHA

**KERN**

### Application:

Thanks to its compact and robust design, bright display and high precision, this series is ideal for use in laboratories, quality control settings, production and in schools and teaching, e.g. biology, chemistry and physics lessons

### Execution:

- Thanks to its compact and robust design, bright display and high precision, this series is ideal for use in laboratories, quality control settings, production and in schools and teaching, e.g. biology, chemistry and physics lessons
- Large, impact-resistant weighing tray made of stainless steel, easy and hygienic to clean
- Especially flat design
- Ergonomically optimised control panel with buttons and high-contrast LCD display
- Secure and non-slip placement with rubber feet
- Level and foot screws for precise levelling of the scales come as standard, producing the most accurate weighing results
- CAL calibration program for setting accuracy
- compact all-round model

### Delivery:

with mains adapter



<b>Art. no.</b>	<b>49000 002</b>
<b>Brand</b>	KERN
<b>Manufacturer Part Number</b>	EHA 3000-0
<b>Type description</b>	EHA 3000-0
<b>Max. weight measuring range</b>	3000 g
<b>Digit increment, weight</b>	1 g
<b>Plate size</b>	120 x 120 mm
<b>Material of cover panel</b>	Stainless steel
<b>With unit counting</b>	Yes
<b>Min. item weight</b>	10 g
<b>Reproducibility</b>	3 g
<b>Linearity</b>	2 g
<b>Housing dimensions (LxWxH)</b>	225 x 160 x 50 mm
<b>Gross Weight</b>	0.750 kg
<b>Product Group</b>	447

### EAN

4045761229532