

Padlock series 85

Precision cylinder lock with key cylinder




Execution:

- Lock made of solid brass, springs and interior parts made of rustproof material
- All nickel-plated steel shackles are case-hardened to protect against attacks, with NANO Protect coating for extremely high corrosion protection
- Automatic function - shackle can be snapped into place without inserting the key
- High number of truly keyed to differ locks
- An off-centre key profile increases the security of the locking mechanism from manipulation
- Ident. No. 062-064, 086-087, 106-107 with extra-high U-bar

Delivery:

2 keys per lock



Art. no.	50025 055
Brand	ABUS
Manufacturer Part Number	80629
Model	85/30
Bracket diameter	5 mm
Shackle height clearance	16.5 mm
Type of closure	Keyed different
Lock type	Padlock
Shackle width clearance	16 mm
Material of padlock shackle	Steel
Material of housing	Brass
Housing width	30 mm
Colour	Brass coloured
With corrosion protection	Yes
With plastic sleeve	No
Gross Weight	0.180 kg
Product Group	5BF

EAN

4003318090455