


40aLSP Steckschlüsseinsätze

HPQ

- für Außen Spline-Drive-Schrauben
- lang, tief ausgebohrt
- MS-33787, MIL-W-8982
- HPQ®-Hochleistungsstahl, verchromt



Code	Spline Gr.	"	d ₁ mm	d ₂ mm	d ₃ mm	L mm	t ₁ mm	t ₂ mm	g	
01021007	7	7/32	8,6	10,7	5	50,8	6	42,8	18	1
01021008	8	1/4	9,5	10,7	5,6	50,8	8	42,8	24	1
01021010	10	5/16	11,6	11,6	7,1	50,8	8	40,8	27	1

402aSP Gelenk-Steckschlüsseinsätze

HPQ

- für Außen Spline-Drive-Schrauben
- MS-33787, MIL-W-8982
- HPQ®-Hochleistungsstahl, verchromt



Code	Spline Gr.	"	d ₁ mm	d ₂ mm	d ₃ mm	L mm	t ₁ mm	t ₂ mm	g	
01542016	8	1/4	9,5	12,7	5,6	32	6,4	9,8	16	5
01542020	10	5/16	11,6	12,7	7,1	35	8	13	18	5

41K Schraubendrehereinsätze


- für Schlitzschrauben
- Klingen nach DIN 5264
- Chrome-Alloy-Steel, verchromt



Code	mm	L ₁ mm	L ₂ mm	d mm	a mm	b mm	g	
01280006	0,6x3,5	28	16	11,6	0,6	3,5	10	5
01280008	0,8x4	28	16	11,6	0,8	4	10	5
01280010	1x5,5	28	16	11,6	1	5,5	11	5
01280012	1,2x8	28	16	11,6	1,2	8	12	5

44 INHEX-Einsätze

- für Innensechskantschrauben
- DIN 7422
- Chrome-Alloy-Steel, verchromt



Code	mm	L ₁ mm	L ₂ mm	d mm	g	
01050003	3	55	30	10,7	20	5
01050004	4	55	30	10,7	20	5
01050005	5	55	30	10,7	25	5
01050006	6	55	30	11,6	30	5

44a INHEX-Einsätze

- für Innensechskantschrauben
- DIN 7422
- Chrome-Alloy-Steel, verchromt

Code	"	L ₁ mm	L ₂ mm	d mm	g	
01450004	1/16	55	30	10,7	11	5
01450005	5/64	55	30	10,7	12	5
01450006	3/32	55	30	10,7	14	5
01450007	7/64	55	30	10,7	17	5
01450008	1/8	55	30	10,7	12	5
01450009	9/64	55	30	10,7	13	5
01450010	5/32	55	30	10,7	14	5
01450012	3/16	55	30	10,7	17	5
01450014	7/32	55	30	10,7	19	5
01450016	1/4	55	30	11,6	24	5

44K INHEX-Einsätze

- für Innensechskantschrauben
- Chrome-Alloy-Steel, verchromt



Code	mm	L ₁ mm	L ₂ mm	d mm	g	
01120003	3	28	16	11,6	10	5
01120004	4	28	16	11,6	10	5
01120005	5	28	16	11,6	10	5
01120006	6	28	16	11,6	10	5
01120008	8	28	16	11,6	15	5

44KTX Schraubendrehereinsätze

- für Innen TORX®-Schrauben
- Chrome-Alloy-Steel, verchromt



Code	Gr.	mm	L ₁ mm	L ₂ mm	d mm	g	
01350008	T8	2,3	28	16	11,6	10	5
01350009	T9	2,5	28	16	11,6	10	5
01350010	T10	2,7	28	16	11,6	10	5
01350015	T15	3,3	28	16	11,6	10	5
01350020	T20	3,8	28	16	11,6	11	5
01350025	T25	4,4	28	16	11,6	11	5
01350027	T27	5,0	28	16	11,6	11	5
01350030	T30	5,5	28	16	11,6	12	5
01350040	T40	6,6	28	16	11,6	12	5

6,3
1/4"

DIN
3120

ISO
1174-1

3