


REV.	DATE	DESCRIPTION
NC	07/14/02	INITIAL RELEASE
A	11/01/05	UPDATE DRAWING FORMAT

5/8-24UNEF-2B (INTERNAL)



QTY	FINISH	MATERIAL	DESCRIPTION
1	NICKEL	BRASS	BODY
1	NATURAL	TEFLON	INSULATOR
1	RED	SILICONE	GASKET

APPROVALS	DATE
DRAWN G.R.S.	11/01/05
CHECKED	
ISSUED	
SHEET 1 OF 1	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [ ] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"

DO NOT SCALE DRAWING	CAD FILE C:/242/242130RP.DWG	DWG. NO. 242130RP.DWG	REV. A	SIZE A	SCALE NA
----------------------	---------------------------------	--------------------------	--------	--------	----------

<b>Amphenol Connex</b>	
PART DESCRIPTION N PLUG TO TNC REVERSE POLARITY JACK ADAPTOR	
PART NO. 242130RP	