

Data sheet Product MK 226 SMD 12 Z SM



PCB connectors>Male headers

Turned precision contacts; ... **packing (option)** - additions:


MK 226 SMD ... SM; ... B SM: 6-40 contacts

MK 226 SMD ... B TR: 6-24 contacts

Features


pitch:	2.54 x 2.54 mm
no. of contacts:	12
contact material:	CuZn-alloy
surface of contact:	tin-plated
surface contact / contact sleeve:	<ul style="list-style-type: none"> • Ni+≥0.2µm Au • Ni+4...6µm Sn
version:	male header
shock resistance:	50 g
volume resistance:	≤10 mΩ
vibration resistance max.:	15 g
capacity between two adjacent contacts:	≤0,4 pF
nominal current:	1.5 A
nominal voltage:	60 V DC
test voltage:	1000 V
insulating body material:	PA 4.6. GF
temperature range:	<ul style="list-style-type: none"> • -40°C... +163°C • (260°C/10 s)
class of inflammability:	UL 94 V-0
specific insulation resistance:	>10 ⁷ Ω·m
connection type:	SMD
reflow solderable:	yes
packing (optional):	bar magazine

Technical Drawing



Equipping

- reel diameter Ø 330 mm



Fischer Elektronik GmbH & Co. KG
 DEUTSCHLAND • GERMANY • ALLEMAGNE

Nottebohmstraße 28
 58511 Lüdenscheid

Telefon +49 2351 435-0
 Telefax +49 2351 45754

info@fischerelektronik.de
 www.fischerelektronik.de