



**Dimensions**

Positions	A	B	C	D	E
9	30.81	24.99	16.92	16.33	11.08
15	39.14	33.32	25.50	24.66	19.39
25	53.04	47.04	38.96	38.38	33.24
37	69.32	63.50	55.42	54.84	49.86

Insulator: Glass-filled thermoplastic PBT, UL94V-0 rated  
 Contact: Male: Brass  
 Female : Phosphor bronze  
 Shell: Steel  
 Contact resistance: 20mOhm max. at 1A DC  
 Insulation resistance: 1000Mohm at 500V DC  
 Dielectric withstanding voltage: 1000V AC/rms, 60Hz for 1 minute  
 Current rating: 5A  
 Voltage rating: 250V AC7rms, 60Hz

Änderung	Datum	Name	Datum	Name	Benennung	
		Bearb.	17.05.00	Hellwig	<b>D-Sub Connector</b> Footprint: 9.4mm  A-D(S)F ...../KKG-T1	
		Gepr.	17.05.00	<i>[Signature]</i>		
		Norm.				
<b>ASSMANN</b> Electronic Components					Zeichnungsnummer <b>ASS 0143B CO</b>	Blatt <b>1/1</b>
					Ersatz für ASS 0146 CO vom 11.11.1997	Blatt