

Pluggable Terminal Blocks

5.08 mm Pitch



FEATURES:

Polarised Mouldings

Withstand Voltage - AC1500V/1min

Pin/Terminal - Tin plated brass

Screw/Torque - M2.5 Steel, Nickel Plated 0.4Nm

Recommended PCB hole size ϕ 1.7 mm

Guided pin alignment



SPECIFICATION:

Gender of contacts	Female
Rated current to EN	15 A
Pitch	5.08 mm
Component type	Wire socket 90°
Termination type	Screw Connection
Connection direction	vertical
Rated voltage to EN	300 V
Combustibility class	UL 94 V-0
Colour	green
Temperature range	-40...+105 °C
Cross-section max.	2.0 mm ²
Cross-section min.	0.33 mm ²
Connection cross-section	0.33-2 mm ² (22-14AWG)

PRODUCT RANGE:

Art. Nr.	Poles	A	Length
RND 205-00177	2	10.2 mm	10.2 mm
RND 205-00178	3	15.2 mm	15.2 mm
RND 205-00179	4	20.3 mm	20.3 mm
RND 205-00180	5	25.4 mm	25.4 mm
RND 205-00181	6	30.5 mm	30.5 mm
RND 205-00183	8	40.6 mm	40.6 mm
RND 205-00184	9	45.7 mm	45.7 mm

