



2-conductor/2-pin, double-deck carrier terminal block; 2-conductor/2-pin ground terminal block; PE; without marker carrier; green-yellow housing; internal commoning

Item No.: 2020-2207



Marking

RoHS ✓
Compliant

Business data

<i>Supplier</i>	WAGO
<i>Item no.</i>	2020-2207
<i>GTIN / EAN</i>	4050821049517
<i>Content</i>	1

Notes


Technical data

Miscellaneous

<i>Ratings per</i>	IEC/EN 60947-7-2
<i>Type of wiring</i>	Front-entry wiring
<i>Total number of connection points</i>	2
<i>Total number of potentials</i>	1

Technical data	
<i>Number of levels</i>	2
<i>Connection technology</i>	Push-in CAGE CLAMP®
<i>Actuation type</i>	Operating tool
<i>Connectable conductor materials</i>	Copper
<i>Nominal cross section</i>	1 mm ²
<i>Solid conductor</i>	0.14 ... 1.5 mm ² / 24 ... 16 AWG
<i>Solid conductor, push-in termination</i>	0.5 ... 1.5 mm ² / 20 ... 16 AWG
<i>Fine-stranded conductor</i>	0.14 ... 1.5 mm ² / 24 ... 16 AWG
<i>Fine-stranded conductor with ferrule, push-in termination, f</i>	0.5 mm ² / 20 AWG
<i>Strip length</i>	9 ... 11 mm / 0.35 ... 0.43 Inch
<i>Width</i>	3.5 mm / 0.138 Inch
<i>Height from upper-edge of DIN-35 rail</i>	51.3 mm / 2.02 Inch
<i>Depth</i>	80.1 mm / 3.154 Inch
<i>Design</i>	horizontal
<i>Type of mounting</i>	Carrier rail 35 x 15
<i>Potential marking</i>	PE
<i>Marking level</i>	Side marking
<i>Color</i>	green-yellow
<i>Insulating material</i>	Polyamide 66 (PA 66)
<i>Fire load [MJ]</i>	0.181 [MJ]
<i>Weight [g]</i>	10.86 [g]
<i>Product Family</i>	X-COM S
<i>Main product function</i>	Multilevel terminal blocks
<i>Product type</i>	Pluggable rail-mount terminal blocks

Images & drawings



Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.