




EDOGH080MSS00.5E08 (PG9)

Connection technology



1: O-ring

Product characteristics

Adapter socket

M12 connector

PG 9 - M12

Electrical data

Electrical design

AC/DC

Operating voltage [V]

30 AC / 36 DC

Environment

Ambient temperature [°C]

-25...90

Protection

IP 67

Mechanical data

Design

straight

Housing materials

Brass nickel-plated

Weight [kg]

0.03

Electrical connection

Connection

PVC cable / 0.5 m;
8 x 0.25 mm² (14 x Ø 0.15 mm)

Wiring

Core colours

BN brown

BU blue

GN green



GY grey

PK pink

RD red

WH white

YE yellow



Colours to DIN 47100

Remarks

Pack quantity

[piece]

1