


E11795



Wirable socket

SDOAA030MSSFKPG





Application	
Special feature	Free from silicone; Gold-plated contacts
Free from silicone	yes
Electrical data	
Operating voltage [V]	< 250 AC
Max. current load total [A]	4; (...40 °C)
Operating conditions	
Ambient temperature [°C]	-25...85
Protection	IP 67
Mechanical data	
Weight [g]	25
Dimensions [mm]	35 x 20 x 30
Materials	PA
Material nut	brass, nickel-plated
Remarks	
Pack quantity	1 pcs.
Electrical connection	
terminals: ...0.75 mm ² ; Cable sheath: Ø 4...6 mm	
Electrical connection - socket	
Connector: 1 x 1/2", angled; Moulded body: PA; Locking: brass, nickel-plated; Contacts: gold-plated	

E11795

Wirable socket

SDOAA030MSSFKPG



Connection

