

Part no.: 50138358
KY-HS-DDS-D9AJ2ARAA-020-T1
Interconnection cable




Figure can vary

Contents

- Technical data
- Electrical connection

Technical data

Basic data	
Suitable for	HS 66x8
Suitable for interface	RS 232


Connection	
Connection 1	
Type of connection	RJ41
Connection 2	
Type of connection	Sub-D
Type	Female
No. of pins	9 -pin
Design	Axial
Connection 3	
Type of connection	Connector
Thread size	Pluggable
Type	Female
No. of pins	2 -pin
Design	Axial
Cable properties	
Number of conductors	6 Piece(s)
Sheathing color	Black
Shielded	Yes
Cable diameter (external)	6 mm
Cable length	2,000 mm
Sheathing material	TPU

Classification	
Customs tariff number	85444290
eCl@ss 8.0	27279218
eCl@ss 9.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855

Electrical connection

Connection 1	
Type of connection	RJ41

Pin	Pin assignment
1	Shield
2	n.c.
3	GND
4	TXD
5	RxD
6	CTS




Part no.: 50138358 – KY-HS-DDS-D9AJ2ARAA-020-T1 – Interconnection cable

Pin	Pin assignment
7	+5 V DC
8	RTS
9	n.c.
10	n.c.

Connection 2	
Type of connection	Sub-D
Function	
Type	Female
No. of pins	9 -pin
Design	Axial

Pin	Pin assignment
1	Shield
2	TXD
3	RxD
4	n.c.
5	GND
6	n.c.
7	CTS
8	RTS
9	+5 V DC



Connection 3	
Type of connection	Connector
Thread size	Pluggable
Type	Female
No. of pins	2 -pin
Encoding	
Design	Axial

