

HEATER 24 V, 60 W HG 04013.0-00



Figure similar

Model		
product brand name		SIVACON
Product designation		heater unit
General technical data		
Active power consumption / Rated value	W	60
Voltage		
Continuous heat output / at 20 °C	W	60
Protection class		
Protection class IP		IP44
Main circuit		
<b>Operating voltage</b>		
• Rated value / minimum	V	24
• Rated value / maximum	V	24
• with AC / at 50 Hz / Rated value / maximum	V	24
• with AC / at 60 Hz / Rated value / maximum	V	24
Product details		
<b>Product component</b>		
• blower		No
• Thermostat		No
Mechanical Design		
Height	mm	140
Width	mm	70

Depth	mm	60
-------	----	----

## Certificates

### Equipment marking

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

R  
E

## General Product Approval



## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR21106AA>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR21106AA/all>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8MR21106AA](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR21106AA)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015