

## Han 3A Protect Cover



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 003 5427
Specification	Han 3A Protect Cover
HARTING eCatalogue	<a href="https://b2b.harting.com/09200035427">https://b2b.harting.com/09200035427</a>

### Identification

Category	Accessories
Series of hoods/housings	Han A <sup>®</sup>
Type of accessory	Protection cover
Description of the accessory	for cable to cable housing
	Metal
	With fixing cord
	With seal

### Version

Size	3 A
Locking type	Single locking lever
Details	for mounted female insert or for mounted Han-Brid <sup>®</sup> insert

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44
	IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	12

### Material properties

Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e



**Pushing Performance**  
Since 1945

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	10
Net weight	20 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140038950
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors