


DEBUR AND BREAK SHARP EDGES

DO NOT SCALE DRAWING

REVISION



PART No.	"L"
TRPST-1-01	1.6
TRPST-2-01	3.2
TRPST-3-01	4.8
TRPST-4-01	6.4
TRPST-5-01	7.9
TRPST-6-01	9.5
TRPST-7-01	11.1
TRPST-8-01	12.7
TRPST-9-01	14.3
TRPST-10-1	15.9

A DRAWN

- NOTES
- MATERIAL: PA66 UL94 V2;
PA66 UL94 V0;
 - COLOR: NATURAL
 - ROHS Compliant;
 - Hole: $\phi 2.54 \pm 0.08\text{mm}$,
Panel Thickness: 1.63mm



DESIGN RIGHT. TR FASTENINGS LTD, 2003
UNDER NO CIRCUMSTANCES MUST THIS
DRAWING BE COPIED OR DISCLOSED,
WITHOUT FIRST OBTAINING WRITTEN
AUTHORITY.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MILLIMETERS
SURFACE FINISH:
TOLERANCES:

ISO 2768 m

NAME	DATE
DRAWN MARTIN ELLIOTT	10/07/14
CHK'D	
APPV'D	

CUSTOMER PART No

MATERIAL:

SEE NOTES

HEAT TREATMENT

N/A

FINISH:

N/A

TITLE:


PUSH SPACER
TEAR DROP

DWG NO.

TRPST-XX-01

A3

PROJECTION



SHEET 1 OF 1