





Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Rotary head
Product compatibility	XCKT XCMD XCKP XCKD
Associated lever	ZCE61 ZCE71

Associated body	ZCP39 ZCMD81L2 ZCMD61M12 ZCMD29L1 ZCMD81L1 ZCD21M12 ZCD29 ZCP31 ZCMD37L5 ZCT21N12 ZCT28N12 ZCMD21L2 ZCT21G11 ZCP35 ZCMD39L1 ZCMD29L2 ZCD27 ZCD39 ZCD28 ZCMD21L1 ZCMD21L08U78 ZCT27P16 ZCP28 ZCP27 ZCMD21L5 ZCT26N12 ZCMD21C12 ZCD35 ZCMD41L5 ZCMD39L2 ZCT27N12 ZCMD21M12 ZCD31 ZCD29M12 ZCMD25L1 ZCP21 ZCT25P16 ZCT28G11 ZCT25N12 ZCMD29L5 ZCMD69C12 ZCD26 ZCT28P16 ZCP29M12 ZCMD29C12 ZCP37 ZCP25 ZCT27G11 ZCMD21L08R12 ZCP29 ZCD37 ZCMD41L2 ZCT25G11 ZCMD25L2 ZCD21 ZCP21M12 ZCD25 ZCT26P16 ZCMD61C12 ZCT26G11 ZCMD81L5 ZCP26 ZCMD39L5 ZCMD25L5 ZCMD37L1 ZCMD41L1 ZCT21P16 ZCMD37L2
Movement of operating head	Rotary
Type of operator	Stay put without operating lever stay put metal
Type of approach	Lateral approach, 2 directions

Complementary

Switch actuation	By specific cam
Positive opening	Without

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22413 - LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	00785901615200
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	0.160 dm
Package 1 width	0.320 dm
Package 1 Length	0.480 dm

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------