

## ToLEDo LifeStyle G190 GOLDEN DIMMABLE

ToLEDo LifeStyle G190 GL DIM 250LM E27 SL

0029982



### Product features

- New state-of-the-art designer lamps for decorative and hospitality applications
- Unconventional design that looks good on both off and on
- Flexible LED filament construction
- Dimming functionality helps to vary lighting scene as lamps can be dimmed from 100% to 10% and reduce energy consumption
- Low power - only 4W
- Lumen output - 150lm
- 2000K colour temperature to create an intimate atmosphere
- Good colour rendering - CRI 80
- 15,000 hours average rated life. Last 15 times longer than incandescent lamps
- Perfectly complements Sylvania E27 SylPendant range available in brass, copper, white and black finish
- Omni-directional light distribution
- More than 100,000X switching cycles
- 3 years warranty



## PRODUCT OVERVIEW

Product name	ToLEDo LifeStyle G190 GL DIM 250LM E27 SL
Technology	LED
Watt (Rated) (W)	4
Type	LED exchangeable
Fixture rating	Open
General application	Hospitality
ETIM Class	EC001959
Warranty	3 years
Luminous flux (lm)	250
Colour temperature (K)	2000
Light colour	Candlelight
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Photobiological Risk Group	RG0
Wattage (W)	4
Product Voltage (V)	230
Dimmable	Yes
Average life (Nominal) (h)	15000
Product EAN number	5410288299822

## DATA TABLE

### General data

Product name	ToLEDo LifeStyle G190 GL DIM 250LM E27 SL
Technology	LED
Watt (Rated) (W)	4
Type	LED exchangeable
Fixture rating	Open

## ToLEDo LifeStyle G190 GOLDEN DIMMABLE

ToLEDo LifeStyle G190 GL DIM 250LM E27 SL

0029982

General application	Hospitality
Operating temperature range (°C)	-20°C...+40°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001959
Warranty	3 years

### Optical data

Luminous flux (lm)	250
Luminous flux (Rated) (lm)	250
Colour temperature (K)	2000
Light colour	Candlelight
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Photobiological Risk Group	RG0
Lumen maintenance at end of nominal life (%)	70

### Electrical data

Wattage (W)	4
Equivalent watt (W)	25
Starting time (max) (s)	<0.5
Warm-up time to 60% of full light (max) (s)	<2.0
Product Voltage (V)	230
Lamp power factor	0.7
Control gear required	No
No. Of switching cycles before premature failures	>100000
Transformer required	No
Dimmable	Yes
Inrush Current (A)	1.42
Lamp Energy Label (class)	G
Max. Luminaires per 10A C Breaker	227
Max. Luminaires per 16A C Breaker	363
Max. Luminaires per 20A C Breaker	454

### Lifetime data

Lifespan L70 B50	15000
Average life (Nominal) (h)	15000
Average life (Rated) (h)	15000

### Physical data

Nominal Product Length (mm)	184
Nominal Product Diameter (mm)	190
Weight (kg)	0.221

### Packaging

Single packaging type	Carton
Product EAN number	5410288299822

## ToLEDo LifeStyle G190 GOLDEN DIMMABLE

ToLEDo LifeStyle G190 GL DIM 250LM E27 SL


0029982

Packaging single length / height (cm)	22.5
Packaging single width (cm)	21.0
Packaging single depth (cm)	21.5
DUN14 (outer)	15410288299829
Units per outer package	2
Packaging outer length / height (cm)	46.5
Packaging outer width (cm)	22.5
Packaging outer depth (cm)	23.0


### Safety data

Optimal operating condition (°C)	-20-40
Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Safety message	Not Suitable for totally enclosed fixtures
Safety message	Dimmable with approved dimmers

## PHOTOMETRY



## TECHNICAL DRAWINGS



ToLEDo LifeStyle G190 GOLDEN DIMMABLE  
*ToLEDo LifeStyle G190 GL DIM 250LM E27 SL*  
0029982



**4**  
kWh/1000h




2019/2015

ToLEDo LifeStyle G190 GOLDEN DIMMABLE  
*ToLEDo LifeStyle G190 GL DIM 250LM E27 SL*  
0029982



0029982



**4**  
kWh/1000h



2019/2015