

## Sylproof Superia LED G3 Emergency SYLPROOF SUPERIA LED G3 1500mm Twin 4K E3 0048723



### Product features

- Sylproof Superia, integrated LED weatherproof luminaire, with UV stabilized flat diffuser and linear prisms designed to achieve uniform lit appearance, optimise light output and to reduce glare, stainless steel diffuser clips and fixing brackets for surface and wall mounting. Polycarbonate housing, Polycarbonate diffuser, Non dimmable, 3 hour emergency, 4000K, CRI80, 7100 lm, 49 W, 135 lm/W, nominal average life (h):50000, energy class: A++ A+ A Class I, IK08, IP65.



### PRODUCT OVERVIEW

Product name	SYLPROOF SUPERIA LED G3 1500mm Twin 4K E3
Technology	LED
Housing	PC Polycarbonate
Mount	Ceiling surface mounting
Fixture rating	Enclosed
General application	Logistics & Industry
ETIM Class	EC000109
Warranty	5 years
Fixture luminous flux (lm)	7100
Luminaire efficacy (lm/W)	135
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Beam Angle (°)	100
Photobiological Risk Group	RG1
Luminous flux (emergency) (lm)	285
Luminous flux (emergency) (lm)	200
Total power consumption (W)	49
Electrical protection	Class I
Control gear type	Electronic ballast
Dimmable	No
Dimming method	N/A
Housing colour	Grey
IP rating	IP65
IK rating	IK08
Product EAN number	5410288487236

### DATA TABLE

#### General data

Product name	SYLPROOF SUPERIA LED G3 1500mm Twin 4K E3
Technology	LED

## Sylproof Superia LED G3 Emergency

*SYLPROOF SUPERIA LED G3 1500mm Twin 4K E3*  
0048723

Housing	PC Polycarbonate
Mount	Ceiling surface mounting
Fixture rating	Enclosed
General application	Logistics & Industry
Operating temperature range (°C)	0°C...+30°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC000109
Warranty	5 years

### Optical data

Fixture luminous flux (lm)	7100
Luminaire efficacy (lm/W)	135
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Beam Angle (°)	100
Photobiological Risk Group	RG1
Luminous flux (emergency) (lm)	285
Luminous flux (emergency) (lm)	200
Emergency duration (h)	3

### Electrical data

Total power consumption (W)	49
Mains voltage (V)	220-240V
Electrical protection	Class I
Control gear required	No
Control gear type	Electronic ballast
Dimmable	No
Dimming method	N/A
Drive current (mA)	300
Glow Wire Test (°C)	850
Nominal Frequency (Hz)	50/60Hz

### Lifetime data

Lifespan L70 B50	60000
Lifespan L80 B10	60000
Lifespan L90 B50	60000

### Physical data

Housing colour	Grey
IP rating	IP65
IK rating	IK08
Diffuser finish	Transparent
Diffuser material	PC Polycarbonate
Nominal Product Length (mm)	1578
Nominal Product Width (mm)	110
Nominal Product Height (mm)	78
Weight (kg)	2.6

## Sylproof Superia LED G3 Emergency SYLPROOF SUPERIA LED G3 1500mm Twin 4K E3 0048723





### Packaging

Single packaging type	Carton
Product EAN number	5410288487236
Packaging single length / height (cm)	137.2
Packaging single width (cm)	11.6
Packaging single depth (cm)	8.4
DUN14 (outer)	05410288487236
Units per outer package	1
Packaging outer length / height (cm)	137.2
Packaging outer width (cm)	11.6
Packaging outer depth (cm)	8.4

### Safety data

Optimal operating condition (°C)	0-30
Dry applications use only	No

## PHOTOMETRY



## TECHNICAL DRAWINGS

## Sylproof Superia LED G3 Emergency *SYLPROOF SUPERIA LED G3 1500mm Twin 4K E3* 0048723

---

