

face milling cutter 45° M1200 Mini
for indexable milling inserts HN.J 0704..., XNGJ 0704..



Application:

excellent face milling cutter range to enhance the performance of machines with ISO40 steep taper and driven units.

Execution:

- state-of-the-art technology with 12 effective cutting edges
- low cost per cutting edge, high productivity
- one range for machining all plane surfaces
- with internal cooling
- 45° setting angle



Art. no.	16041 124
Brand	WIDIA
Manufacturer Part Number	3958007
Min. cutting edge diameter	100 mm
Max. cutting edge diameter	108.7 mm
Length	50 mm
Bore diameter	32 mm
max. ap	3.5 mm
Number of cutting edges	9 PCS
Gross Weight	2.300 kg
Product Group	1XJ

EAN

4021169654862