

Electronic pocket vernier callipers

IP67

ORION[®]

Application:

For measuring external, internal, step and depth dimensions.

Execution:

- ON/OFF
- Zero setting at any position
- mm/inch switch-over

Advantage:

- Depth gauge: flat design with narrow probe tip, length 22 mm, for depth measurements in small boreholes from 2.5 mm diameter

Delivery:

In a case, with battery (1 x 3 V lithium type CR 2032)



Art. no.	31177 130
Brand	ORION
Manufacturer Part Number	31177 130
Min./max. length measuring range	0-300 mm
Depth gauge rod	Flat
IP protection class	IP 67
Length of jaw	60 mm
Length of cross tips	21 mm
Digit increment	0.01 mm
Digit increment in inches	0.0005 in
Type of locating	With locking screw
With automatic shut off	No
Battery designation	3V CR2032 Lithium
Number of rechargeable batteries/batteries	1 PCS
Weight of rechargeable battery/battery	0.003 kg
Battery voltage	3 V
Type of rechargeable battery/battery	Lithium
Calibration Group	A
ISO	13385-1
Gross Weight	0.658 kg
Product Group	3BH

EAN

4053625306220