

Electronic pocket vernier callipers

IP67 for special applications



Application:

For measuring shaft grooves.

Execution:

- ON/OFF
- Zero setting at any position
- mm/inch switch-over
- Auto off
- ABS function

Advantage:

- Key lock to prevent unintentional adjustment

Delivery:

In a case, with battery (1 x 3 V lithium type CR 2032)



Art. no.	31181 415
Brand	MAHR
Manufacturer Part Number	4103074
Min./max. length measuring range	0-150 mm
Data transmission type	multiCOM
Depth gauge rod	Round
IP protection class	IP 67
Length of jaw	40 mm
Digit height	11 mm
Length of cross tips	16.5 mm
Digit increment	0.01 mm
Digit increment in inches	0.0005 in
Depth gauge rod thickness	1.5 mm
Type of locating	With locking screw
Battery designation	3V CR2032 Lithium
Number of rechargeable batteries/batteries	1 PCS
Weight of rechargeable battery/battery	0.003 kg
Battery voltage	3 V
Type of rechargeable battery/battery	Lithium
Calibration Group	A
ISO	13385-1
Gross Weight	0.392 kg
Product Group	305

EAN

4059192002305