

Platform trolley series 600 with front wall, zinc-plated

The surface of the loading area is covered with sheet steel, load capacity 500 kg



Execution:

- The surface of the loading area is covered with 2 mm electrolytically zinc-plated sheet steel
- Loading area height 260 mm
- Push handle made of 25 mm steel tubing
- 2 fixed castors and 2 castors made of solid rubber 200 x 50 mm
- Galvanised
- The 600 series includes platform trolleys, table trolleys, platform trolleys with front wall, box trolleys and bar-type trolleys.



Art. no.	50260 022
Brand	KONGAMEK
Manufacturer Part Number	KM632-3B
Colour	Silver coloured
Load-carrying capacity	500 kg
Material of loading surface	Steel plate
Type	With front wall
Length	1200 mm
Width	800 mm
Height	900 mm
Number of fixed rollers	2
Loading surface length	1200 mm
Loading surface size	1200 x 800 mm
Number of steering rollers	2
Loading-surface height	260 mm
Loading-surface width	800 mm
Length x width x height	1200 x 800 x 900 mm
With wheel lock	Yes
Wheel width	50 mm
Wheel diameter	200 mm
Material of wheel	Solid rubber
Surface	Zinc plated
Gross Weight	45.500 kg
Product Group	5AT

EAN

7350050357825