

## Pneumatic hose PUR

With fabric inlay



### Execution:

- Shell made of ester-based polyurethane
- Polyester fibre fabric inlay
- Inner and outer layers made of polyester fibres
- Resistant to oil, solvents and non-aqueous solutions
- Straight version

### Advantage:

- High elasticity, extremely flexible
- Long service life
- Excellent resistance to oil, solvents and non-aqueous solutions



<b>Art. no.</b>	<b>75391 020</b>
<b>Brand</b>	CEJN
<b>Manufacturer Part Number</b>	199581220
<b>Inner hose diameter</b>	8 mm
<b>Outer diameter of hose</b>	12 mm
<b>Hose length</b>	50 m
<b>Min./max. temperature conditions</b>	-30 to +60 °C
<b>Max. operating pressure</b>	16 bar
<b>Burst pressure</b>	64 bar
<b>Material of hose</b>	Polyurethane/polyester fibres
<b>Colour</b>	Blue
<b>Gross Weight</b>	4.350 kg
<b>Product Group</b>	7AI

### EAN

7391390087850