

Han 24B Ex-HSE-M25 4 pegs



Part number	19 36 024 1521
Specification	Han 24B Ex-HSE-M25 4 pegs
HARTING eCatalogue	https://b2b.harting.com/19360241521

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] Ex
Type of hood/housing	Hoods

Version

Locking type	Double locking lever
Size	24 B
Version	Side entry
Cable entry	1x M25
Field of application	Connectors for explosion hazardous environments
Details	ATTENTION! Only to be used with Han [®] Ex inserts!

Technical characteristics

Limiting temperature	-20 ... +40 °C
Degree of protection acc. to IEC 60529	IP65 With cable gland

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 5015 (sky blue)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Commercial data

Packaging size	1
----------------	---



Pushing Performance

Commercial data

Net weight	566.5 g
Country of origin	China
Customs tariff number	8538900000
