



Nr. / No.	Länge / Length (m)
93017	1.00
50856	2.00

USB 2.0 Hi-Speed Kabel

- USB-A Stecker > USB-B 90° Winkelstecker
- USB Standard: High Speed USB 2.0
- Innenleiter: 2xAWG24 + 2xAWG28 Kupfer
- Isolierung: PVC
- Schirmung: doppelt
- Datenrate: max. 480Mbit/s
- Gewicht: 93017: 31g
50856: 40g
- RoHS-konform

USB 2.0 Hi-Speed cable

- USB-A plug > USB-B 90° angled plug
- USB Standard: High Speed USB 2.0
- Inner conductor: 2xAWG24 + 2xAWG28 copper
- Insulation: PVC
- Shielding: double
- Data rate: max. 480Mbps
- Weight: 93017: 31g
50856: 40g
- RoHS compliant

Änderungen

Änderungen		Datum	Name
Datum	Name	gez.:	13.09.2011
23.04.2014	tf	gepr.:	13.09.2011
		Norm:	
Änderungen vorbehalten / Subject to change			

Bezeichnung	Blatt
USB AB 90° HiSpeed 2.0	
Zeichnungs-Nr.:	von
V2	

