

JT-JDS2915

Signal generator and frequency meter



The JT-JDS2915 is compact and able to be used on the go with an optionally available power bank.

MAIN FEATURES

Channels	2 Channel generator 1 Channel frequency meter
Frequency range	1–100 MHz
Frequency meter	1–100 MHz
Sine	0 - 15 MHz
Square, triangle	0 - 15 MHz
TTL, pulse	0 - 6 MHz
Signal forms	Sine, square, triangle, pulse, half-, wave, exponential rise/ fall, etc.
Frequency accuracy	± 20 ppm
Frequency stability	± 1 ppm/3h
Sampling rate	266 MSa/s
Size	145 x 95 x 55 mm
Items delivered	Generator, BNC signal terminals, power supply

FURTHER SPEZIFICATIONS

Display	2,4 inch TFT color LCD
Vertical wave resolution	14 bits
Amplitude range	<10MHz: 0-20 VPP >10 MHz: 0-10 VPP
Amplitude resolution	1 mV
Amplitude stability	± 5%/5h
Amplitude flatness	<10MHz: ± 5%
Impedance of output	50Ω ±10%

FURTHER DETAILS

Article number	JT-JDS2915
EAN	4250236817071
Costums tariff no.	85432000